


# UltraFoil CFA

## Technical Data Sheet

**CFA - Top Coated Clear, Food Contact Compliant, Biaxially Oriented Polypropylene Film for Facestock Applications.**



### Features

- Dedicated print and foil receptive top coat
- Superior fine tone and foiling performance
- Excellent clarity for 'no-label look'
- High gloss surface
- Excellent hot/cold moisture resistance
- For rigid or semi-squeeze containers
- High stiffness for conversion and automatic dispensing
- Balanced biaxial orientation for superior die cutting

### Printability

**UltraFoil CFA** utilises a proprietary aqueous top coating to give superior narrow web print and foil performance. The tailored surface allows enhanced detail for finer tone work and intricate foiling designs for maximum brand enhancement. UltraFoil CFA is compatible with a wide range of print and foil processes including flexography, gravure, letterpress, offset and screen. Exact ink and adhesive systems should be recommended by your supplier. For optimum foiling performance corona treatment is recommended.



### Technical Properties (Typical Values)

Property	Test Method	Test Conditions	Units	CFA	
Thickness	Innovia Films test		micron	51	59
			gauge	200	230
Yield	Innovia Films test		m <sup>2</sup> /kg	21.9	18.8
			in <sup>2</sup> /lb	15400	13200
			g/m <sup>2</sup>	45.6	53.2
Optical: Gloss Haze (wide angle)	Innovia Films test	45° 2.5°	%	90	
				<3.0	
Tensile strength	ASTM D 882	Strain rate 50%/min	MN/m <sup>2</sup>	MD	200
				TD	180
			kpsi	MD	29.0
				TD	26.1
Elongation at break	ASTM D 882	Strain rate 50%/min	%	MD	105
				TD	120
Elasticity modulus (1% secant)	ASTM D 882	Strain rate 10%/min	MN/m <sup>2</sup>	MD	2400
				TD	2200
			kpsi	MD	348
				TD	319
Dimensional stability	Innovia Films test	60 secs at 120°C (248°F)	%	MD	3.0
				TD	Nil
		60 secs at 130°C (266°F)		MD	6.0
				TD	1.0

MD Machine Direction TD Transverse Direction

All properties are tested under standard laboratory conditions: 23 ± 2°C, 50 ± 5% RH, (73 ± 4F, 50 ± 5% RH), unless otherwise stated. Where relevant, tests are based on international testing standards.

Rayoface™ CFA- 1 of 2 - 0120



*use our imagination...*

# UltraFoil CFA

## Technical Data Sheet

### Conversion

High machine direction stiffness and tensile strength afford fast, efficient self adhesive lamination, enhanced printing press registration, matrix stripping and superior high speed label dispensing. Die cutting performance and reduced die wear are aided by the balanced orientation properties of the facestock film.

### Reel Specifications

#### Nominal Reel Diameters

Film	Core Size/(mm)	Approx Outside Dia/(mm)	Length/(metres)
CFA51	153	805	9300
		930	12300
CFA59	153	864	9300

Film	Core Size/(in)	Approx Outside Dia/(in)	Length/(feet)
CFA200	6	31.7	30500
		36.6	40350
CFA230	6	34.0	30500

Alternative reel lengths/core sizes are available subject to negotiation.

The print coating is available on either the inner or outer surface of Ultrafoil CFA.

### Film Storage and Handling

Care should be taken to protect reels of film from storage temperatures above 30°C (86°F) and localised sources of heat above 45°C (113°F). Reels of UltraFoil CFA should be protected from high levels of moisture and accidental water splashes at all times. The reels should remain in the protective coverings supplied until ready for use on converting machinery. Converted reels, in both master and slit reel form should be similarly protected at all times. UltraFoil CFA is suitable for use for 6 months from the date of delivery and stocks should be used in rotation. Films should be allowed to reach operating room temperatures for 24 hours before use.

### Food contact

UltraFoil CFA complies with the applicable EU and US legislation for most applications involving direct contact with foods. Full details are given on the Declaration of Compliance. Customers intending to use UltraFoil CFA in a food contact application should request a copy of this document from Innovia Films. Details of compliance with food contact legislation in non-EU countries are also available upon request.

### Health & Safety Guidelines

For Health & Safety information, please refer to literature reference L190.

**Disclaimer:** Innovia Films or any of its affiliated companies (hereinafter 'Innovia Films') declines any liability with respect to the use made by any third party of the information contained herein. The information contained herein represents Innovia Films' best knowledge thereon without constituting any express or implied guarantee or warranty of any kind (including, but not limited to, the accuracy, the completeness or relevance of the data set out herein). Innovia Films is the sole owner or authorised user of the intellectual property rights relating to the information communicated. The information relating to the use of the products is given for information purposes only. No guarantee or warranty is provided that the product is adapted to the client's specific use. The client should perform his own tests to determine the suitability for a particular purpose. The final choice of use of a product remains the sole responsibility of the client.

UltraFoil CFA – 2 of 2 - 0120

#### Regional Offices:

Europe (UK) Tel +44 16973 42281

Americas (USA) Tel +1 800 424 6273

Asia-Pacific (Aus) Tel +61 3 9303 0600

[www.innoviafilms.com](http://www.innoviafilms.com)

email: [labels@innoviafilms.com](mailto:labels@innoviafilms.com)

™ Trademark of Innovia Films

